


CU 600V PVC THHN PVC Control Cable Type TC-ER

Type TC-ER Control Cable 600Volt Copper Conductors, Polyvinyl Chloride (PVC) with nylon layer Insulation THHN Polyvinyl Chloride (PVC) Jacket with 1 Insulated Green CU Ground, Control Cable Conductor Identification Method 1 Table 2



Images not to scale. See Table for Dimensions

CONSTRUCTION:

- Conductor:** 7 strands class B compressed bare copper per ASTM B3 and ASTM B8 for 14, 12, and 10 AWG cables. 26 strands class K bare copper per ASTM B3 and B174 for 16 AWG cables
- Insulation:** Polyvinyl Chloride (PVC) with nylon layer THHN, 19 Mils thick for 16, 14, 12 AWG cables and 24 Mils for 10 AWG cables, Type TFFH for 16 AWG cable and Type THHN or THWN for 14, 12, 10 AWG cables
- Grounding Conductor:** Class B compressed stranded copper with green insulation
- Filler:** Polypropylene filler on cables with 5 or less conductors
- Binder:** Polyester flat thread binder tape applied for cables with more than 5 conductors
- Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type TC-ER control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C in wet locations and 90°C in dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

SPECIFICATIONS:

- ASTM B3 - Soft or annealed copper
- ASTM B8 - Concentric-lay-standard copper
- UL 83 - Thermoplastic Insulated wires and cables
- UL 1277 - Electrical Power and Control Cable
- UL 1685 - Flame Test
- UL 1581 - Electrical Wires, Cables and Flexible Cords
- IEEE 1202/FT4 - Vertical Tray Flame Test (70,000 Btu/hr) and ICEA T-29-520 - (210,000 Btu/hr)
- ICEA S-73-532 - Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-58-679 - Control Cable Conductor Identification Method 1 Table 2
- ICEA S-95-658 NEMA WC70 - Power cables rated 2000 volts or less for the distribution of electrical energy

SAMPLE PRINT LEGEND:

SOUTHWIRE EXXXXX #P# (UL) [#AWG Or #kcmil] CU THHN PVC/PVC 600V Type TC-ER For CT USE SUN. RES. For DIRECT BURIAL FT4 YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire[®]

Measurements and Electrical Data

#16 AWG

Stock Code	Cond. Number	Dia. Over Cond. (1)	Ground	Jacket Thickness	Approx. OD (6)	Copper Weight	Approx. Weight	Min Bending Radius	DC Resis. @ 25°C	AC Resis @ 90°C	Allowable Ampacities*
		inches	No.xAWG	mils	inches	lbs./MFT	lbs./MFT	inches	Ω/MFT	Ω/MFT	Amps
TBA	3	0.056	1 x 16	45	0.318	32	69	1.3	4.180	5.226	10/10/10
TBA	4	0.056	1 x 16	45	0.345	40	82	1.4	4.180	5.226	10/10/10

Measurements and Electrical Data

#14 AWG

Stock Code	Cond. Number	Dia. Over Cond. (1)	Ground	Jacket Thickness	Approx. OD (6)	Copper Weight	Approx. Weight	Min Bending Radius	DC Resis. @ 25°C	AC Resis @ 90°C	Allowable Ampacities*
		inches	No.xAWG	mils	inches	lbs./MFT	lbs./MFT	inches	Ω/MFT	Ω/MFT	Amps
606806 [◇]	3	0.070	1 x 14	45	0.350	51	93	1.4	2.630	3.288	14/15/15
606814 [◇]	4	0.070	1 x 14	45	0.380	64	113	1.5	2.630	3.288	14/15/15

All dimensions are nominal and subject to normal manufacturing tolerance.

* Ampacities are based on Table 310.15 (B)(16) of the NEC, 2014 Edition. Ampacities of insulated conductors rated up to and including 2000 Volts, based on ambient temperature of 30°C (86°F) and assuming ground is also carrying current.

◇ Standard stock item



Measurements and Electrical Data

#12 AWG

Stock Code	Cond. Number	Dia. Over Cond. (1)	Ground	Jacket Thickness	Approx. OD (6)	Copper Weight	Approx. Weight	Min Bending Radius	DC Resis. @ 25°C	AC Resis @ 90°C	Allowable Ampacities*
		inches	No.xAWG	mils	inches	lbs./MFT	lbs./MFT	inches	Ω/MFT	Ω/MFT	Amps
606723 [◇]	3	0.087	1 x 12	45	0.392	81	131	1.6	1.660	2.075	16/20/20
606798 [◇]	4	0.087	1 x 12	45	0.428	102	160	1.7	1.660	2.075	16/20/20

Measurements and Electrical Data

#10 AWG

Stock Code	Cond. Number	Dia. Over Cond. (1)	Ground	Jacket Thickness	Approx. OD (6)	Copper Weight	Approx. Weight	Min Bending Radius	DC Resis. @ 25°C	AC Resis @ 90°C	Allowable Ampacities*
		inches	No.xAWG	mils	inches	lbs./MFT	lbs./MFT	inches	Ω/MFT	Ω/MFT	Amps
605543 [◇]	3	0.111	1 x 10	45	0.473	130	199	1.9	1.040	1.300	24/28/30
606863 [◇]	4	0.111	1 x 10	45	0.519	162	244	2.1	1.040	1.300	24/28/30

All dimensions are nominal and subject to normal manufacturing tolerance.

* Ampacities are based on Table 310.15 (B)(16) of the NEC, 2014 Edition. Ampacities of insulated conductors rated up to and including 2000 Volts, based on ambient temperature of 30°C (86°F) and assuming ground is also carrying current.

◇ Standard stock item

