


1/C CU 8KV 140 NL-EPR 133% TS SIMpull® PVC MV-105

Type MV-105 Single Conductor Copper, 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, SIMpull® Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Images not to scale. See Table 1 for Dimensions

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 140 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Stripable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 8KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or annealed copper
- ASTM B8 Concentric-lay-standard copper
- UL 1072 - Medium Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable & ICEA S-97-682 5-46 KV Utility
- UL 1685/FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 AWG and Larger)
- IEEE 1202 -Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 AWG and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- CSA C68.10 - Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C22.2 No.230 - Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 - Cable Test Methods

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTING BOLT] #P# (UL/CSA) 1/C [#AWG or #kcmil] CU 140 MILS NL-EPR 8KV 133% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. TC-ER(CSA 1/0 LARGER) FOR DIRECT BURIAL FT4 -ST1 YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



Southwire®

Table 1 – Weights & Measurements

Stock Code	Cond. Size AWG	Diameter over			Jacket Thickness ¹ mils	Approx. OD (6) inches	Approx. Weight lbs./MFT	Max Pull Tension lbs.	Min Bending Radius inches	Conduit Size* inches
		Cond. (1) inches	Insul. (3) inches	Insul. Shield inches						
TBA	2	0.283	0.600	0.660	65	0.810	489	531	9.7	2.5
TBA	1	0.322	0.639	0.699	65	0.849	558	670	10.2	2.5
TBA	1/0	0.362	0.679	0.739	80	0.919	671	845	11.0	3
TBA	2/0	0.405	0.722	0.782	80	0.962	779	1065	11.5	3
TBA	3/0	0.456	0.773	0.833	80	1.013	914	1342	12.2	3
646573	4/0	0.512	0.829	0.889	80	1.069	1079	1693	12.8	3
646576	250	0.558	0.884	0.944	80	1.124	1226	2000	13.5	3.5
567142	350	0.661	0.987	1.047	80	1.227	1591	2800	14.7	3.5
646579	500	0.789	1.115	1.175	80	1.355	2122	4000	16.3	4
646580	750	0.968	1.303	1.363	80	1.543	2995	6000	18.5	5
TBA	1000	1.117	1.452	1.512	80	1.692	3846	8000	20.3	5

All dimensions are nominal and subject to normal manufacturing tolerances

* Conduit size based on 3 phase 40% fill-factor without ground

¹ Comply with ICEA S-93-639 Appendix C for jacket thickness determination

Table 2 – Electrical and Engineering Data

Stock Code	Cond. Size AWG	Resistance		Reactance		Positive Sequence Impedance*	Zero Sequence Impedance*	Shield Short Circuit Current 6 Cycles Amps	Allowable Ampacities 90°C/105°C	
		DC @ 25°C Ω/MFT	AC @ 90°C Ω/MFT	X _C @ 60Hz MΩ*MFT	X _L @ 60Hz Ω/MFT				In Duct † Amps	In Air ‡ Amps
TBA	2	0.162	0.203	0.041	0.046	0.203 + j0.046	0.572 + j0.487	2180	155 / 165	195 / 215
TBA	1	0.129	0.161	0.037	0.044	0.162 + j0.044	0.532 + j0.466	2307	175 / 185	225 / 250
TBA	1/0	0.102	0.128	0.034	0.043	0.128 + j0.043	0.499 + j0.446	2437	200 / 215	260 / 290
TBA	2/0	0.081	0.101	0.031	0.042	0.102 + j0.042	0.473 + j0.425	2577	230 / 245	300 / 335
TBA	3/0	0.064	0.081	0.028	0.040	0.081 + j0.040	0.451 + j0.402	2743	260 / 275	345 / 385
646573	4/0	0.051	0.064	0.026	0.039	0.065 + j0.039	0.433 + j0.379	2925	295 / 315	400 / 445
646576	250	0.043	0.054	0.025	0.038	0.055 + j0.038	0.420 + j0.357	3104	325 / 345	445 / 495
567142	350	0.031	0.039	0.022	0.036	0.040 + j0.036	0.398 + j0.321	3439	390 / 415	550 / 610
646579	500	0.022	0.028	0.019	0.034	0.029 + j0.034	0.376 + j0.283	3855	465 / 500	685 / 765
646580	750	0.014	0.020	0.016	0.032	0.020 + j0.032	0.350 + j0.237	4467	565 / 610	885 / 990
TBA	1000	0.011	0.016	0.014	0.031	0.016 + j0.031	0.331 + j0.208	4952	640 / 690	1060 / 1185

* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(69) of the 2014 National Electrical Code (40°C Ambient Air Temperature)

