


1/C CU 15KV 220 NL-EPR 133% TS SIMpull® PVC MV-105

Type MV-105 Single Conductor Copper, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, SIMpull® Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Images not to scale. See Table 1 for Dimensions

CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Stripable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or annealed copper
- ASTM B8 Concentric-lay-standard copper
- UL 1072 - Medium Voltage Power Cables
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable & ICEA S-97-682 5-46 KV Utility
- UL 1685/FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 AWG and Larger)
- IEEE 1202 -Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 AWG and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- CSA C68.10 - Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- CSA C22.2 No.230 - Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 - Cable Test Methods

SAMPLE PRINT LEGEND:

SOUTHWIRE [SYMBOL - LIGHTNING BOLT] #P# (UL/CSA) 1/C [#AWG or #kcmil] CU 220 MILS NL-EPR 15KV 133% INS LEVEL 25% TS MV-105 FOR CT USE SUN. RES. TC-ER(CSA 1/0 LARGER) FOR DIRECT BURIAL FT4 -ST1 YEAR (NESC) [SEQUENTIAL FEET MARKS]



Southwire®

Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Table 1 – Weights & Measurements

Stock Code	Cond. Size AWG	Diameter over			Jacket Thickness ¹ mils	Approx. OD (6) inches	Approx. Weight lbs./MFT	Max Pull Tension lbs.	Min Bend- ing Radius inches	Conduit Size* inches
		Cond. (1)	Insul. (3)	Insul. Shield						
		inches	inches	inches						
953638 [◊]	2	0.283	0.760	0.820	80	1.000	639	531	12.0	3
955104	1	0.322	0.799	0.859	80	1.039	715	670	12.5	3
955989 [◊]	1/0	0.362	0.839	0.899	80	1.079	809	845	12.9	3
955997 [◊]	2/0	0.405	0.882	0.942	80	1.122	922	1065	13.5	3.5
956003	3/0	0.456	0.933	0.993	80	1.173	1063	1342	14.1	3.5
956011 [◊]	4/0	0.512	0.989	1.049	80	1.229	1235	1693	14.7	3.5
956029 [◊]	250	0.558	1.044	1.104	80	1.284	1390	2000	15.4	4
956037 [◊]	350	0.661	1.147	1.207	80	1.387	1767	2800	16.6	4
956045 [◊]	500	0.789	1.275	1.335	80	1.515	2314	4000	18.2	5
643755 [◊]	600	0.866	1.361	1.421	80	1.601	2680	4800	19.2	5
956052 [◊]	750	0.968	1.463	1.523	80	1.703	3210	6000	20.4	5
956060 [◊]	1000	1.117	1.612	1.672	110	1.912	4183	8000	22.9	6
581886	1250	1.250	1.767	1.827	110	2.067	5074	10000	24.8	6
567443	1500	1.370	1.930	1.990	110	2.164	5853	12000	26.2	
550811	2000	1.583	2.138	2.198	110	2.438	7682	16000	29.3	

All dimensions are nominal and subject to normal manufacturing tolerances

* Conduit size based on 3 phase 40% fill-factor without ground

¹ Comply with ICEA S-93-639 Appendix C for jacket thickness determination

◊ Standard stock item

Table 2 – Electrical and Engineering Data

Stock Code	Cond. Size AWG	Resistance		Reactance		Positive Sequence Impedance*	Zero Sequence Impedance*	Shield Short Circuit Current 6 Cycles Amps	Allowable Ampacities 90°C/105°C	
		DC @ 25°C	AC @ 90°C	X _c @ 60Hz	X _L @ 60Hz				In Duct †	In Air ‡
		Ω/MFT	Ω/MFT	MΩ*MFT	Ω/MFT				Amps	Amps
953638 [◊]	2	0.162	0.203	0.053	0.051	0.203 + j0.051	0.573 + j0.418	2700	155 / 165	195 / 215
955104	1	0.129	0.161	0.049	0.049	0.162 + j0.049	0.531 + j0.400	2827	175 / 185	225 / 250
955989 [◊]	1/0	0.102	0.128	0.045	0.047	0.128 + j0.047	0.496 + j0.383	2957	200 / 215	260 / 290
955997 [◊]	2/0	0.081	0.101	0.042	0.045	0.102 + j0.045	0.467 + j0.366	3097	230 / 245	300 / 335
956003	3/0	0.064	0.080	0.039	0.043	0.081 + j0.043	0.443 + j0.346	3263	260 / 275	345 / 385
956011 [◊]	4/0	0.051	0.064	0.036	0.042	0.065 + j0.042	0.423 + j0.327	3445	295 / 315	400 / 445
956029 [◊]	250	0.043	0.054	0.034	0.041	0.055 + j0.041	0.409 + j0.309	3624	325 / 345	445 / 495
956037 [◊]	350	0.031	0.039	0.030	0.039	0.040 + j0.039	0.384 + j0.279	3959	390 / 415	550 / 610
956045 [◊]	500	0.022	0.028	0.026	0.037	0.029 + j0.037	0.361 + j0.248	4376	465 / 500	685 / 765
643755 [◊]	600	0.018	0.024	0.024	0.036	0.348 + j0.229	0.024 + j0.036	4655	505 / 544	765 / 855
956052 [◊]	750	0.014	0.019	0.022	0.035	0.020 + j0.035	0.334 + j0.210	4987	565 / 610	885 / 990
956060 [◊]	1000	0.011	0.015	0.020	0.034	0.016 + j0.034	0.315 + j0.185	5472	640 / 690	1060 / 1185
581886	1250	0.009	0.013	0.019	0.033	0.014 + j0.033	0.298 + j0.165	5976	715 / 770	1210 / 1350
567443	1500	0.007	0.011	0.017	0.032	0.012 + j0.032	0.286 + j0.151	6363	790 / 850	1331 / 1485
550811	2000	0.005	0.010	0.016	0.032	0.011 + j0.032	0.263 + j0.127	7183	940 / 1010	1575 / 1755

* Calculations are based on three cables triplexed / 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(77) Detail 1. of the 2014 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(69) of the 2014 National Electrical Code (40°C Ambient Air Temperature)

◊ Standard stock item

